

ULTRA CLEAN AND DRY DELIVERY

FMS-1/350-P

FMS-G70-BPE



RETENTION OF PARTICLES

ELEMENT TECHNICAL SPECIFICATIONS FMS-1/350-P

Efficiency	Beta 4>4193 (ISO 16889:99)			
DHC	3000 grams (MTD)			
Maximum Pressure	150 psi			
Recommended Flow	350 gpm			
Dimensions	42x6.25x6.25"			
Weight	21 lbs			
Housings	FMS-350-BP			



WATER / EMULSIONS COALESCENCE REMOVAL




ELEMENT TECHNICAL SPECIFICATIONS FMS-C70-BPE

Efficiency	98.6% SAE J1488 Certified		
DHC	Drain		
Maximum Flow	80 gpm		
Recommended Flow	70 gpm		
Dimensions	40x6x6"		
Weight	18 lbs		
Housings	FMS-C70-BP		

THETA 4>4310 SINGLE PASS TEST		PARTICLES		
	ISO CODES	4 μm	6 µm	14 µm
Reservoir Contaminant Level	22/21/18	31898	14071	542
Average Cleanliness at Downstream	10/8/6	7.4	1.7	0.34

Contamination control at dispatch is a fundamental part of best practice. Our bottom-connected lockbox filters are the only ones that can be installed on the ridge of subway tanks and handle multiple dispensing guns.



Water and emulsions cause up to 15% of power loss, thus up to 15% increase in fuel consumption. All ISO 4406 contamination control plans must contemplate water and emulsions with SAE J1488 certified systems.



SCAN TO VISIT OUR WEBSITE



FMS INTERNATIONAL INC.



